
Fittings and accessories for CO₂-solidification process

The illustration shows the complete equipment required for manual gassing by means of a shower head.

Electric heater, preventing freezing, 220 V complete with 3-pole plug and 2 m long cable ltem No. 221.001 100 Watt, gas flow appr. 10 Nm³/h ltem Nor. 221.002 500 Watt, gas flow appr. 24 Nm³/h Other type upon request!

1a) Spares

Item No. 221.003 = 2 m long cable with plug
Item No. 221.004 = spare heating element 100 Watt
Item No. 221.005 = spare heating element 500 Watt



with spring safety valve

Cylinder pressure manometer Working pressure manometer 0 - 315/200 kp/cm²

neter 0 - 16/10 kp/cm²



electric heater

CO₂-cylinder

pressure reducer

shower head


elbow

3) Dosing unit Item No. 221.007

Comprising:

control unit with built-in-timer and contactor, range 2 to 60 sec., solenoid valve 1/4", pilot lamp, button, armored cable, length 2 meters, between unit and button and 2 m long rubber cable with plug between unit and 220 V mains.

It is imperative to ensure that **only the reduced pressure** (working pressure) is admitted to the unit.



4) Pistol Item No. 221.008

to be connected to hose, 10 mm ins. dia., with 5/8" connector

4a) Suitable rubber seal - Item No. 221.009



5) Brass elbow Item No. 221.010

with 5/8" connection nut and M 12x1 connector



6) Rubber shower head with built-in nozzle

internal thread M 12x1

Item No.	221.011	221.013	221.014	221.015
Diameter	60 mm	130 mm	115 mm	135 mm
Colour	red	black	red	red



7) Brass lance

with 5/8" connection nut

Item No.	Dia.	Length	
221.016	4 mm	400 mm	
221.017	4 mm	600 mm	
221.018	6 mm	400 mm	

Item No.	Dia.	Length
221.019	6 mm	600 mm
221.020	6 mm	800 mm
221.021	6 mm	1000 mm



8) Co₂-hose Item No. 221.022

orange-red

Inside dia. 10 mm, wall thickness 3 mm

